

SVクラスプ C-move



★ D103HA
ハーフアラシ
7~9.5mm用



★ D258HA
ハーフアラシ
7~9mm用



★ CMD272HA
ハーフアラシ
7~9mm用



★ D104Z
CZ×7
7~9.5mm用



★ CMM634G
7.5~9mm用



★ CMM634
7.5~9mm用



★ K601
8~10mm用



★ K602
8~10mm用



★ K603
8~10mm用



★ D301
10~12mm用



★ D303
10~12mm用

SVクラスプ C-move (2連)



★ M7371G-2
6~7mm用



★ M7377G-2
6~7mm用



★ M6262-2
4.5~5.5mm用



★ M6263-2
4.5~5.5mm用



★ M7371-2
6~7mm用



★ M7377-2
6~7mm用



★ M632-2
7~8mm用



★ M634-2
7~8mm用



★ M637-2
7~8mm用



★ M331-2
8~9mm用



★ M335-2
8~9mm用

SVクラスプ C-move (3連)



★ M7373-3
3~4mm用



★ M7374-3
3~4mm用



★ M7377-3
3~4mm用



★ M637-3
3.5~4.5mm用



★ M639-3
3.5~4.5mm用



★ M331-3
5~7mm用



★ M335-3
5~7mm用



★ M336-3
5~7mm用



★ M337-3
5~7mm用

SV 両面クラスプ

※内部のパネを除き、全てSV925仕上げ
(オールシルバー・ノンニッケル)



★ KS01 S
5~6.5mm用



★ KS02 S
5~6.5mm用



★ KS03 S
5~6.5mm用



★ KS01 M
7~9mm用



★ KS02 M
7~9mm用



★ KS03 M
7~9mm用

[All SV・Non Ni] クラスプ 使用方法

プラグ挿入口の反対側を掴まむと、プラグが抜けます。



棒プラグ

- デコレーション：SILVER ■プラグ：SILVER
- 楕円カン：SILVER ■内部部品：ステンレス
- メッキ：ロジウムメッキ (ニッケルメッキ不使用)